

# Cylinder Holding Devices

OSHA regulations require compressed gas cylinders to be secured from toppling when in storage or in use. The devices shown here will help you comply with these regulations.

## Model LN400 Wall Mount Cylinder Holder

This cast aluminum cylinder holder provides an easy way to secure cylinders to a wall, in a gas storage cabinet, or other stable surface. The holder is attached with bolts or lag screws using the pre-formed holes 7 inches apart. The holder can be used with cylinders from 4 to 14 inches in diameter. Cylinders are held firmly in place with a nylon strap fitted with a sturdy buckle, an optional steel chain and hook, or both strap and chain.

### How to Order:

Model Number	Description
94254040	LN400 Wall mount cylinder holder with strap

## Model LN420 Bench Type Cylinder Holder

This holder is designed to prevent toppling of cylinders when they are next to a lab or work bench and cannot be secured to a wall. The special screw clamp holds securely to a table top without marring the surface. The holder can be used with cylinders from 4 to 14 inches in diameter. Cylinders are held firmly in place with a nylon strap fitted with a sturdy buckle, an optional steel chain and hook, or both strap and chain.

### How to Order:

Model Number	Description
94254060	LN420 Bench mount cylinder holder with strap

